
Polymer Systems Technology Limited

UK & Ireland Distributor



© 2011 - Polymer Systems Technology Limited TM Unit 2. Network 4. Cressex Business Park, Lincoln Road, High Wycombe, Bucks. HP12 3RF
Phone +44 (0) 1494 446610
Fax: +44 (0) 1494 528611
Web: http://www.siliconepolymers.co.uk

Email: sales@silicone-polymers.co.uk



PCM-7926

Vinyl Crosspolymer

SILICONE TECHNOLOGY

Creative Partners in a Material World

NuSil Technology

1050 Cindy Lane • Carpinteria, CA 93013 805/684-8780 • 805/566-9905 Fax www.nusil.com

An ISO 9001 Certified Company

Product Profile

Description

Dimethyl polymer endblocked with methyl, vinyl, and phenyl groups

$$\begin{array}{c|c} CH_{3} & H_{3}C - Si & CH_{3} \\ I & CH_{3} & CH_{3} \\ CH_{3} & CH_{3} \\ \end{array} \\ \begin{array}{c} H_{3}C - Si & CH_{3} \\ CH_{3} & CH_{3} \\ CH_{3} & CH_{3} \\ \end{array}$$

- Dimethyl methylhydride copolymer endblocked with methyl groups
- Silica

Applications

• As a formulary component in cosmetics applications

Typical Properties	Result	Metric Conv.	ASTM	NT-TM
Uncured:				
Appearance	Translucent	-	D2090	002
Viscosity, Part A	21,000 cP	21,000 mPas	D1084, D2196	001
Viscosity, Part B	16,500 cP	16,500 mPas	D1084, D2196	001
Work Time	3 minutes	-	-	008
Cured: 15 minutes @ 150°C (302°F)				
Specific Gravity	1.07	-	D792	003
Durometer, Type A	20	-	D2240	006
Tensile Strength	550 psi	3.8 MPa	D412	007
Elongation	500%		D412	007

Instructions for Use

Mixing

Part A and Part B mix in a 1:1 ratio when using the static mix and dispense cartridge. Attach a disposable static mix tip to the cartridge and dispense through the static mix head directly on to the substrate.

Adjustable Cure Schedule

Product cures at room temperature and a wide range of elevated temperatures and cure times to accommodate different production needs. Contact NuSil Technology for details.

Cure Inhibition

The cure may be inhibited by traces of amines, sulfur, nitrogen oxide, organotin compounds and carbon monoxide. Because organic rubbers often contain these substances, they should not come in contact with the uncured elastomer. Catalyst residues from silicone RTV elastomers and peroxide-cured silicone elastomers may also inhibit the cure.

Packaging

50 ml SxS Kit

2 Pint Kit (91 g)

2 Gallon Kit (7.28 kg)

Warranty

12 Months

Warnings About Product Safety

NuSil Technology believes the information and the data contained herein are accurate and reliable. However, the user is responsible to determine the material's suitability and safety of use. NuSil Technology cannot know each application's specific requirements and hereby notifies the user that it has not tested or determined this material's suitability or safety for use in any application. The user is responsible to adequately test and determine the safety and suitability for their application and NuSil Technology makes no warranty concerning fitness for any use or purpose. NuSil Technology has completed no testing to establish safety of use in any medical application.

NuSil Technology has tested this material only to determine if the product meets the applicable specifications. (Please contact NuSil Technology for assistance and recommendations when establishing specifications.) When considering the use of NuSil Technology products in a particular application, review the latest Material Safety Data Sheet and contact NuSil Technology with any questions about product safety information.

Do not use any chemical in a food, drug, cosmetic, or medical application or process until having determined the safety and legality of the use. The user is responsible to meet the requirements of the U.S. Food and Drug Administration (FDA) and any other regulatory agencies. Before handling any other materials mentioned in the text, obtain available product safety information and take the necessary steps to ensure safety of use.

Biocompatibility/Skin Sensitivity

Please contact NuSil Technology regarding current data for this product.

Specifications

Do not use the typical properties shown in this technical profile as a basis for preparing specifications. Please contact NuSil Technology for assistance and recommendations in establishing particular specifications.

Patent Warning

NuSil Technology disclaims any expressed or implied warranty against the infringement of any patent. NuSil Technology does not warrant the use or sale of the products described herein will not infringe the claims of any United States' or other country's patents covering the product itself, its use in combination with other products or its use in the operation of any process.

Warranty Information

NuSil Technology's warranty period is 12 months from the date of shipment when stored below 40°C in original unopened containers. Unless NuSil Technology provides a specific written warranty of fitness for a particular use, NuSil Technology's sole warranty is that the product will meet NuSil Technology's then current specification. NuSil Technology specifically disclaims any other expressed or implied warranty, including warranties of merchantability and fitness for use. The exclusive remedy and NuSil Technology's sole liability for breach of warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted. NuSil Technology expressly disclaims any liability for incidental or consequential damages.